



Teflon™ PTFE CFP 6000 X

Fine Powder Fluoroplastic Resin

Product Information

Description

Teflon™ PTFE CFP 6000 X is a polytetrafluoroethylene fine powder resin used primarily for paste extrusion. Teflon™ PTFE CFP 6000 X offers the excellent combination of properties typical of Teflon™ fluoroplastic resins:

- Chemical inertness to nearly all industrial chemicals and solvents
- Superior in-use thermal stability (low thermal instability index)
- Exceptional dielectric properties, stable with frequency and temperature;
- Toughness and flexibility
- Low coefficient of friction
- Non-stick characteristics
- Negligible moisture absorption
- Excellent weather resistance
- Service temperature up to 260 °C (500 °F)
- Useful properties at -240 °C (-400 °F)
- Moderate stiffness and high ultimate elongation

Teflon™ PTFE CFP 6000 X is designed for processing at medium to high reduction ratios (250:1–3000:1). It is particularly suitable for production of wire coating, jacketing, and tubing at fast sintering rates with superior thermal stability in use.

Teflon™ PTFE CFP 6000 X meets the requirements of ASTM D4895, Type I, Grade 3, Class C.

Typical Applications

Teflon™ PTFE CFP 6000 X is designed for use as wire and cable insulation and small diameter, thin wall tubing.

Processing

Teflon™ PTFE CFP 6000 X is extruded using a liquid processing aid such as naphtha. In the paste extrusion process, the powder is mixed with a lubricant aid and then compressed into a cylindrical preform slug under light pressure (1.5–2.0 MPa [220–290 psi]). The preform slug is placed in the cylinder of a paste extruder, where the composition is forced under high pressure through a finishing die to produce beading, tubing, or wire coatings. After extrusion, the product is a low-density, but coherent, fibrous structure. Teflon™ PTFE CFP 6000 X is usually processed further, with heat, into a solid resin product such as tubing. Heat is applied in two steps, which may be taken in-line with extrusion or separately. The lubricant must be removed first, usually by heating within the range of 100–300 °C (212–572 °F). A sintering step follows to melt the resin above its melting point of approximately 342 °C (648 °F) and produce the void-free, solid PTFE resin.

Food Contact Compliance

Properly processed products (sintered at high temperatures common to the industry) made from Teflon™ PTFE CFP 6000 X resin can qualify for use in contact with food in compliance with FDA 21 CFR 177.1550 and European Regulation (EU) No. 10/2011. For details and information, please contact your Chemours representative.

Safety Precautions

Before processing any fluoroplastics, read the Safety Data Sheet, available upon request from our Customer Service Group at (844) 773-CHEM/2436 in the U.S. or (302) 773-1000 outside of the U.S. Also read the detailed information in the latest edition of the "Guide to the Safe Handling of Fluoropolymer Resins," published by the Fluoropolymers Division of The Society of the Plastics Industry (www.fluoropolymers.org) or by PlasticsEurope (www.plasticseurope.org).

Storage and Handling

Teflon™ PTFE fine powder resins must be handled carefully to avoid shearing the powder prior to extrusion. Fibrillation by shearing is not reversible, and damaged particles can appear as defects in the finished product. As temperature is reduced below the transition point of 19 °C (66 °F), the powder becomes progressively less sensitive to mechanical damage or compaction in its containers.

Chemours recommends that powder compacted during shipping and storage be restored to its optimum condition by cooling it for one or two days below 19 °C (66 °F), followed by screening through a 2–4.76 mm opening sieve (4–10 mesh). Lumps that are retained on the sieve that can be broken up by shaking at temperatures below 19 °C (66 °F) may be used; however, harder lumps that cannot be broken up should be discarded.

All processing steps prior to preforming should be done at reduced temperature, but ambient dew point must be controlled to prevent condensation on the resin. Storage and handling facilities should be clean to avoid any cross-contamination. The high sintering temperature causes even very small foreign particles to become visible and/or cause defects in finished products. Keep resin drums closed and clean.

Packaging

Teflon™ PTFE CFP 6000 X resin is packaged in 25-kg (55.1-lb) plastic containers. For convenient shipment, orders of 300-kg (661.4-lb) pallets (12 drums) are recommended.

Typical Property Data for Teflon™ PTFE CFP 6000 X Fine Powder Fluoroplastic Resin*

Property Test	Test Method		Unit	Typical Value
Average Particle Size	ASTM D4895	ISO 12086	µm	500
Bulk Density	ASTM D4895	ISO 12086	g/L	460
Standard Specific Gravity	ASTM D4895	ISO 12086		2.183
Thermal Instability Index	ASTM D4895	ISO 12086		<15
Extrusion Pressure at RR = 1600:1	ASTM D4895	ISO 12086	MPa (psi)	41.4 (6,000)
Melt Peak Temperature				
Initial	ASTM D4895	ISO 12086	°C (°F)	342 (648)
Second	ASTM D4895	ISO 12086	°C (°F)	325 (617)

Teflon™ PTFE CFP 6000 X meets the requirements of ASTM D4895-15, Type I, Grade 3, Class C.

*Typical properties are not suitable for specification purposes.

HOW TO USE THE TEFLON™ BRAND NAME WITH YOUR PRODUCT

Teflon™ is a registered trademark of Chemours for its brand of fluoroplastic resins, coatings, films, and dispersions. The Teflon™ brand name is licensed by Chemours in association with approved applications. Without a trademark license, customers may not identify their product with the Teflon™ brand name, as Chemours does not sell such offerings with the Teflon™ trademark. Unlicensed customers may refer to the Chemours product offering with only the Chemours name and product code number descriptor as Chemours sells its product offerings. There are no fair use rights or exhaustion of rights to use the Teflon™ trademark from buying from Chemours, a Chemours customer, or a distributor without a trademark license from Chemours.

If you are interested in applying for a trademark licensing agreement for the Teflon™ brand, please visit www.teflon.com/license

CAUTION: Do not use Chemours materials in medical applications involving permanent implantation in the human body or contact with bodily fluids or tissues, unless the material has been provided from Chemours under a written contract that is consistent with Chemours policy regarding medical applications and expressly acknowledges the contemplated use. For further information, please contact your Chemours representative. For medical emergencies, spills, or other critical situations, call (866) 595-1473 within the United States. For those outside of the United States, call (302) 773-2000.

The information set forth herein is furnished free of charge and based on technical data that Chemours believes to be reliable. It is intended for use by persons having technical skill, at their own discretion and risk. The handling precaution information contained herein is given with the understanding that those using it will satisfy themselves that their particular conditions of use present no health or safety hazards. Because conditions of product use are outside our control, Chemours makes no warranties, express or implied, and assumes no liability in connection with any use of this information. As with any material, evaluation of any compound under end-use conditions prior to specification is essential. Nothing herein is to be taken as a license to operate under or a recommendation to infringe any patents.

NO PART OF THIS MATERIAL MAY BE REPRODUCED, STORED IN A RETRIEVAL SYSTEM OR TRANSMITTED IN ANY FORM OR BY ANY MEANS ELECTRONIC, MECHANICAL, PHOTOCOPYING, RECORDING OR OTHERWISE WITHOUT THE PRIOR WRITTEN PERMISSION OF CHEMOURS.

For more information, visit teflon.com/industrial

For sales and technical support contacts, visit teflon.com/industrialglobalsupport

© 2016 The Chemours Company FC, LLC. Teflon™ and any associated logos are trademarks or copyrights of The Chemours Company FC, LLC. Chemours™ and the Chemours Logo are trademarks of The Chemours Company.

Replaces: K-26132

C-10142 (2/16)